

Installation Instructions
Instrucciones de Instalación /
Instructions d'installation /
Installationsanleitung /
Istruzioni per l'installazione

TRIPP LITE
SERIES

**USB-C Multiport Adapter,
4K/60 Hz HDMI, 5G USB Hub,
140W PD Charging**

U444-06N-H4U-C3

**Adaptador Multipuerto USB-C, 4K/60 Hz
HDMI, Hub USB 5 G, Carga PD de 140 W**

**Adaptateur multiport USB-C, HDMI 4K/60
Hz, Hub USB 5G, charge PD 140 W**

**USB-C Multiport Adapter, 4K/60 Hz HDMI,
5G USB Hub, 140 W PD-Aufladung**

**Adattatore multiporta USB-C, HDMI 4K/60
Hz, 5G hub USB, ricarica PD 140 W**



Purchased product may differ from image.

El producto comprado puede diferir de la imagen.

Le produit acheté peut différer de l'image.

Das gekaufte Produkt kann vom Bild abweichen.


Il prodotto acquistato potrebbe differire dall'immagine.

Eaton

Powering Business Worldwide

Installation

Instalación / Installation /
Installation / Installazione



Installation

Instalación / Installation / Installation / Installazione

- ➊ USB-C 5G or Max PD
140W Input
- ➋ HDMI Display (4K/60 Hz)
- ➌ USB 5G Device Max 5V
1.5 A
- ➍ USB-C Host PC

Español

- ➊ Entrada USB-C 5 G o
Máx. PD de 140 W
- ➋ Pantalla HDMI (4K/60 Hz)
- ➌ Dispositivo USB 5 G Máx.
5 V 1.5 A
- ➍ PC Anfitrión USB-C

Français

- ➊ Entrée USB-C 5G ou Max
PD 140 W
- ➋ Affichage HDMI
(4K/60 Hz)
- ➌ Dispositif USB 5G Max
5 V 1,5 A
- ➍ PC hôte USB-C

Deutsch

- ➊ USB-C 5G oder Max PD
140 W Eingang
- ➋ HDMI-Anzeige (4K/60 Hz)
- ➌ USB 5G Gerät Max 5 V
1,5 A
- ➍ USB-C-Host-PC

Italiano

- ➊ ingresso USB-C 5 G o
Max PD 140 W
- ➋ display HDMI (4K/60 Hz)
- ➌ dispositivo USB 5G Max 5
V 1,5 A
- ➍ PC host USB-C

Refer to your cable's Owner's Manual for complete installation and operation instructions.

Consulte el Manual del Usuario de su cable para ver las instrucciones completas de instalación y funcionamiento.

Reportez-vous au manuel d'utilisation de votre câble pour obtenir des instructions complètes d'installation et d'utilisation.

Vollständige Installations- und Betriebsanweisungen finden Sie in der Bedienungsanleitung Ihres Kabels.

Faccia riferimento al Manuale d'uso del suo cavo per le istruzioni complete sull'installazione e il funzionamento.

Eaton has a policy of continuous improvement. Specifications are subject to change without notice. Photos and illustrations may differ slightly from actual products.



Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2024 Eaton
All Rights Reserved
Publication No.
24-03-118 /
93-4A7F_RevA
June 2024

Eaton is a registered trademark.

All trademarks are property of their respective owners.